



## Pocket Pro High Range TDS Tester

**Product #:** 9531300  
**AED Price:** Contact Hach

### Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ deliver accurate results with built in diagnostics, replaceable batteries, and a large, easy-to-read LCD screen.

#### Confidence in results

Easy calibration steps take the guesswork out of calibrating the sensor to keep it in optimum condition.

#### Saves time and money

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

#### Ease of use

The large LCD screen is easy to read; backlighting is included on Pocket Pro<sup>+</sup> models, allowing measurement in almost any lighting environment.

---

### Specifications

Accuracy:	2% FS
Backlight:	No
Battery requirements:	4 AAA
Casing IP rating:	IP67
Manual languages:	English, French, German, Italian, Spanish
Operating temperature range:	0 - 50 °C
Parameter:	TDS, Temp.
Range:	0 - 10.00 ppt
Resolution:	0.01 ppt
Sample volume:	7 mL
TDS factor:	Adjustable; 0.71 default
Warranty:	24 months
What's included?:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.

---

### What's included?

Includes: tester, 4 AAA batteries, lanyard and quick start guide.