



## Pocket Pro+ Multi 2 Tester for pH/Cond/TDS/Salinity with Replaceable Sensor

**Product #:** 9532800  
**AED Price:** Contact Hach

### Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ are engineered to deliver accurate results. Backed up with built in performance diagnostics, you never have to guess when to clean or calibrate the sensor. You also get replaceable batteries for convenient field use, and a large, easy-to-read LCD screen.

#### Confidence in results

Take the guesswork out of when to calibrate or clean the sensor with built-in diagnostics

#### Saves time and money

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

#### Ease of use

Large LCD screen is easy to read and backlight included in replacement sensor models allow for taking measurements in almost any environment

---

### Specifications

Accuracy:	Sal: $\pm 1\%$
Backlight:	Yes
Battery requirements:	4 AAA
Casing IP rating:	IP67
Manual languages:	English, French, German, Italian, Spanish
Operating temperature range:	0 - 50 °C
Parameter:	pH, Conductivity, TDS, Salinity, Temp.
Range:	pH: 0.00 - 14.00 pH
Resolution:	Cond: 0.1 $\mu\text{S}/\text{cm}$ from 0.0 - 199.9 $\mu\text{S}/\text{cm}$ ; 1 $\mu\text{S}/\text{cm}$ from 200 - 1999 $\mu\text{S}/\text{cm}$ ; 0.01 mS/cm from 2.00 - 19.99 mS/cm
Sample volume:	9 mL
TDS factor:	Adjustable; 0.71 default
Warranty:	24 months
What's included?:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.

---

### What's included?

Includes: tester, 4 AAA batteries, lanyard and quick start guide.