



## SIP10 Sipper Set for DR3900 with 1 inch round cell

**Product #:** LQV157.99.10001  
**AED Price:** Contact Hach

Sipper for pour through applications with spectrophotometer DR3900. With dual path length 1 inch/cm round cell, USB cable and pump tubing.

---

### Specifications

Cuvette compatibility:	Dual pathlength Pour-Thru Cell, plastic, 1 inch/1 cm
Dimensions (H x W x D):	120 mm x 85 mm x 200 mm
Flow rate:	1 mL/s
Height:	with cell (85 mm without cell)
Interface:	USB type A
Length:	200 mm
Operating temperature range:	10 - 40 °C at 95% Relative Humidity (non-condensing)
Power requirements (Voltage):	5 V
Power Supply:	USB Cable
Rinsing volume:	Minimum 25 mL
Storage conditions:	-10 °C - 60 °C
Warranty:	24 months
Wavelength range:	340 - 900 nm
Weight:	0.5 kg