



Orbisphere GA2400 Stainless Steel Oxygen Sensor (EC) for 6110 TPO Analyser, 40 bar, EPDM O-rings

Product #: GA2400-S00T

AED Price: Contact Hach

Highly accurate and customisable oxygen measurement for all environments

The Orbisphere GA2400 oxygen (O₂) Electrochemical (EC) sensor is designed for process monitoring as well as laboratory analysis in the liquid or gas phases across.

With its large measuring possibilities the Orbisphere GA2400 O₂ EC-sensor can be used for a wide range of applications from beer or soft-drinks production to rinsing of semiconductor waters in chip-manufacturing plants, reactor coolant systems in nuclear power plants, or any place where oxygen measurement is critical.

A small residual signal with unrivalled accuracy (± 0.1 ppb) is made possible by the exclusive sensor design. Different pre-mounted membrane kits are available to fulfill any particular process requirements and O₂ measurement ranges required.

The stainless steel Orbisphere GA2400-S00T O₂ electrochemical sensor for 6110 TPO analyser is mechanically resistant to pressure up to 40 bar.

Easy and fast maintenance

Traditional cleaning processes can take more than thirty minutes to complete. The GA2400 and GA2800 EX come with an innovative cartridge system that contains everything needed to complete membrane and electrolyte solution change in less than 5 minutes.

Low level oxygen measurement and unrivalled accuracy

The Hach Orbisphere GA2400 and GA2800 EX utilise an electrochemical oxygen sensor with a lower detection level of 0.1 ppb and unrivalled highly accurate readings of $\pm 1\%$. This feature allows users to ensure control of low oxygen levels, for product and equipment integrity and avoiding corrosion.

Robust for harsh environments

The robust stainless steel or Hastelloy design makes the GA2400 and GA2800 EX sensor ideal for the most demanding applications. ATEX certification comes standard in all GA2800 units, making the sensor especially suitable for harsh chemical environments.

Specifications

Accuracy:	Accuracy = Trueness (ISO 57251)
	2935A-A: The greater of $\pm 1\%$ of reading or ± 10 ppb, or ± 20 Pa
	2952A-A: The greater of $\pm 1\%$ of reading or ± 2 ppb, or ± 5 Pa
	2956A-A: The greater of $\pm 1\%$ of reading or ± 0.1 ppb ¹ , or ± 1 ppb ² , or ± 0.25 Pa
	29552A-A: The greater of $\pm 1\%$ of reading or ± 2 ppb, or ± 5 Pa

	¹ Accuracy is ± 0.1 ppb for 410, 510, 362x, 360x and 3655 instruments
	² Accuracy is ± 1 ppb for 366x and 3650 instruments
Body Material:	Stainless Steel
Certifications:	CE
Flow rate:	Recommended flow rate in flow chamber
	2935A-A: 25 mL/min
	2952A-A: 50 mL/min
	2956A-A: 180 mL/min
	29552A-A: 50 mL/min
Material:	O-Rings: EPDM
Measuring range:	Range at 25 °C
	2935A-A: 10 ppb - 400 ppm or 20 Pa - 1,000 kPa
	2952A-A: 1 ppb - 80 ppm or 5 Pa - 200 kPa
	2956A-A: 0.1 ppb - 20 ppm or 0.25 Pa - 50 kPa
	29552A-A: 2 ppb - 80 ppm or 5 Pa - 200 kPa
Model:	GA2400
Pressure range:	40 bar
Pressure resistance:	40 bar minimum with default PPS collar (100 bar with stainless steel collar)
Protection class:	IP66
Response time:	Response time at 25 °C for a 90% signal change
	2935A-A: 2.5 min
	2952A-A: 38 s
	2956A-A: 7.2 s
	29552A-A: 90 s
Sensor material:	Stainless Steel for 6110
Temperature compensation:	-5 - 60 °C
Temperature resistance:	-5 - 100 °C
Warranty:	6 months
Weight:	0.3 kg
Wetted Materials:	Stainless Steel 1.4404 (AISI 316L)
	No O-rings are in contact with the sample
What's included?:	Oxygen Sensor (GA2400-S00T), incl. plastic screw-on storage cap for sensor head protection; protection cap without grille (33051-S0); protection cap with grille (33051-SP)

What's included?

Oxygen Sensor (GA2400-S00T), incl. plastic screw-on storage cap for sensor head protection; protection cap without grille (33051-S0); protection cap with grille (33051-SP)