



Pressurized Sampling Relay Module

Product #:	8520600
AED Price:	Contact Hach

The pressurized sampling relay module has a high-voltage relay for automatic sample collection from a pressurized sample line. The module also has low-voltage connections for optional flow pacing and sampler program control. The module can be used with a portable, refrigerated or an All-Weather Refrigerated Sampler (AWRS) that has the AS950 controller.

Specifications

Cable length:	Auxiliary cable, 7-pin
Certifications:	CE, UL/CSA standards (cETLus)
Dimensions:	160 x 80 x 86 mm (6.30 x 3.15 x 3.39 in.)
Enclosure waterproof rating:	IP66 / NEMA 4X
Operating conditions:	-30° C (-22° F) - 50°C (122°F)
Power input:	12 - 15 V DC, 0.31 A (from the AS950 controller)
Relay functions:	5 A maximum resistive load at 240 VAC, 1/8 HP at 120 VAC, 1/4 HP at 240 VAC
Weight:	0.59 kg (1.3 lbs)