



CPVC Immersion Mount Assembly

Product #:	MH432G
AED Price:	Contact Hach
Available	

Each immersion hardware includes a 1/2-inch diameter x 1.2 m long pipe, 1/2 x 3/4-inch NPT coupling, and plastic pipe-mount junction box with terminal strip. Used for 3700-series and PC/RC series sensors.

Specifications

Diameter:	12.7 mm
Length:	1219 mm
Material:	CPVC
Special notes:	Composition:
	Pipe,
	1/2" / 3/4" NPT adapter coupling,
	plastic pipe-mount junction box with terminal strip