



Insertion Mounting Hardware, 2", Stainless Steel, 3700 Series

Product #: MH118M9NZ
AED Price: Contact Hach
Ships within 1 week

Stainless steel 2" NPT insertion assembly with ball valve. For use with the 3700-series inductive/electrodeless conductivity sensors.

Specifications

Length:	584.2 mm
Material:	stainless steel
Pressure range:	Max 5.5 bar at 95 °C
Process connection:	2 " outer NPT thread for connection to pipes or closed tanks
Temperature range:	-5 - 95 °C