



Pocket Pro Salinity Tester

Product #: 9531600
AED Price: Contact Hach

Take The Guesswork Out of Your Measurements.

Hach Pocket Pro and Pro+ deliver accurate results with built in diagnostics, replaceable batteries, and a large, easy-to-read LCD screen.

Confidence in results

Easy calibration steps take the guesswork out of calibrating the sensor to keep it in optimum condition.

Saves time and money

Easy to replace AAA batteries and convenient sample cup make maintenance and measurements simple

Ease of use

The large LCD screen is easy to read; backlighting is included on Pocket Pro⁺ models, allowing measurement in almost any lighting environment.

Specifications

Accuracy:	1% FS
Backlight:	No
Battery requirements:	4 AAA
Casing IP rating:	IP67
Manual languages:	English, French, German, Italian, Spanish
Operating temperature range:	0 - 50 °C
Parameter:	Salinity, Temp.
Range:	0 - 10.00 ppt
Resolution:	0.01 ppt
Sample volume:	7 mL
Warranty:	24 months
What's included?:	Includes: tester, 4 AAA batteries, lanyard and quick start guide.

What's included?

Includes: tester, 4 AAA batteries, lanyard and quick start guide.