



## Hach pH<sub>D</sub> sc Online Process pH Sensor - General Purpose Sanitary Mount pH Sensor

**Product #:** DPD3P1.99

**AED Price:** Contact Hach

### The smart choice for accurate and reliable online process pH measurement

General Purpose Online Process pH Sensor with Integrated Digital Electronics for "Plug and Play" with Hach Digital SC Controllers - pH<sub>D</sub> Technology, Glass pH Electrode, PEEK Housing, Sanitary Mount, 10 m Cable

This instrument connects to Claros, Hach's innovative Water Intelligence System, enabling you to seamlessly connect and manage instruments, data, and process – anywhere, anytime. The result is greater confidence in your data and improved efficiency in your operations. To unlock the full potential of Claros, insist on Claros Enabled instruments.

#### Exceptional Process pH Sensor Performance with the Differential Electrode pH<sub>D</sub> Measurement Technique

This field-proven technique uses three electrodes instead of the two normally used in conventional pH sensors. Process and reference electrodes measure the pH differentially with respect to a third ground electrode. The end result is unsurpassed measurement accuracy, reduced reference junction potential, and elimination of sensor ground loops. These process pH sensors provide greater reliability, resulting in less downtime and maintenance.

#### Lower Maintenance Needs with the Double Junction Salt Bridge

The double junction salt bridge creates a barrier to contamination which minimizes the dilution of the internal standard cell solution. The result is lower maintenance needs and a longer time period between calibrations.

#### Extended Working Life with the Replaceable Salt Bridge/Protector

The unique, replaceable salt bridge holds an extraordinary volume of buffer to extend the working life of the sensor by protecting the reference electrode from harsh process conditions. The salt bridge simply threads onto the end of the sensor if replacement is needed.

#### Reliability with Built-in Encapsulated Preamp

Encapsulated construction protects the sensor's built-in preamp from moisture and humidity, ensuring reliable sensor operation. The preamp in the pH<sub>D</sub> analog sensor produces a strong signal, enabling the sensor to be located up to 1000 m (3280 ft.) from the analyzer.

#### Innovative Technology

The former GLI, now a Hach Company brand, invented the Differential Electrode Technique for pH measurement in 1970. The pH<sub>D</sub> takes this field-proven technology to a new level.

---

## Specifications

Accuracy:	± 0.02 pH
Cable connection:	Digital
Cable length:	10 m PUR (polyurethane) 4-conductor with one shield, rated to 105°C
Calibration method:	Two point automatic, one point automatic, two point manual, one point manual
Communication:	MODBUS
Compliance:	Hazardous location, Maritime, CE
Drift:	0.03 pH per 24 hours, non-cumulative
Electrode type:	General Purpose
Flow rate:	3 m (10 ft.) per second, maximum

Housing material:	PEEK
Length:	271.3 mm
Measuring range:	-2.0 to 14.0 pH
Mounting:	Sanitary
Operating temperature range:	-5 - 70 °C (23 - 158 °F) pH and ORP  0 - 50 °C (32 - 122 °F) SS pH
	Before initial pH calibration, calibrate the temperature measurement when the sensor is in water or buffer which is at approximately the same temperature as the pH buffers (matches current recommendation)
Pressure range:	Maximum 10.7 bar. 6.9 bar for Digital Sensor at 70°C, and 6.9 bar for Analogue Sensor at 105 °C.
Repeatability:	± 0.05 pH
Sensitivity:	± 0.01 pH
Sensor cable:	10 m (33 ft.) polyurethane, 4-conductor cable with one shield, rated to 105°C (221°F)
Sensor thread:	1" NPT
Special notes:	The sanitary style sensor has an integral 2-inch flange, special cap, and EPDM compound gasket for use with a GLI 2-inch sanitary tee and mounting hardware.
Storage conditions:	4 - 70 °C, 0-95% relative humidity (non-condensing)
Temperature accuracy:	± 0.5 °C (± 0.9 °F)
Temperature compensation:	Automatic with NTC 300 Ω thermistor, or manually fixed at a user-entered temperature,  additional selectable temperature correction factors (ammonia, morpholine, or user-defined pH/°C linear slope) available for pure water automatic compensation 0.0 - 50 °C
Temperature sensor:	NTC 300 Ω thermistor for automatic temperature compensation and analyzer temperature readout
Transmission distance:	100 m (328 ft.), maximum
Warranty:	24 months
Weight:	0.316 kg
Wetted Materials:	PEEK or PPS, salt bridge of matching material with PVDF junction, glass process electrode, titanium ground electrode, and FKM/FPM® O-ring seals (pH sensor with optional HF-resistant glass process electrode has 316 stainless steel ground electrode, and perfluoroelastomer wetted O-rings; consult factory for other available wetted O-ring materials)

---

## Required Accessories

- SC1000 Probe Module, 4 Sensor Connectors, 4 mA Output, 4 Relays, 100-240 VAC, with EU plug (Item LXV400.99.2R121)
- SC1000 Display Module (Item LXV402.99.00001)