



## **Solitax hs-line sc Turbidity (0.001-4000 NTU) and Suspended Solids (0.001-500 g/L) immersion probe, with wiper, stainless steel**

**Product #:** LXV423.99.00200

**AED Price:** Contact Hach

Call for ship date

### **Accurate, colour-independent suspended solids and turbidity measurements**

High-precision process probe to determine turbidity and suspended solids. Colour independent method with a dual-beam infrared/scattered light photometer.

90° turbidity measurement according to DIN EN ISO 7027. The backscatter photoreceptor measures suspended solids accurately in accordance with DIN 37414. A single correction factor replaces time-consuming multipoint calibrations with dilution series. The measurement data is displayed and processed with the help of a controller.

Turbidity measurement performance certified according to MCERTs regulation.

Prognosys is a predictive diagnostic system that allows you to be proactive in your maintenance, by alerting you to upcoming instrument issues. Know with confidence whether changes in your measurements are due to changes in your instrument or your water.

This instrument connects to Claros, Hach's innovative Water Intelligence System, enabling you to seamlessly connect and manage instruments, data, and process – anywhere, anytime. The result is greater confidence in your data and improved efficiency in your operations. To unlock the full potential of Claros, insist on Claros Enabled instruments.

### **Greater accuracy, less maintenance**

Hach Solitax sc sensors provide accurate, colour-independent measurement of turbidity and suspended solids in drinking water, wastewater and industrial process applications. A self-cleaning device prevents biological growth and interference of gas bubbles. This system's reliable performance and full data communication capability help improve process control and reduce treatment costs associated with polymer use, digester volume, and sludge handling.

### **Excellent correlation to laboratory analysis**

Solitax sc sensors show an exceptional correlation to laboratory analysis. On-line measurement not only saves time on manual analysis, but also provides critical real-time measurements that can be used to operate the plant more efficiently.

### **Fully serviceable sensors**

Conventional turbidity and suspended solids sensors are potted and are discarded when they no longer function. Solitax sc sensors are fully serviceable, which often doubles the useful life of the sensor.

### **Easy one-point calibration**

Factory calibrated in conformity with DIN EN ISO 7027 for long-term calibration stability. Calibration is easy with a simple correction factor procedure.

### **Multi-channel, multi-parameter system**

Multiple Solitax sc sensors can be installed on one Hach SC Controller. The same controller can also accommodate any combination of parameters. All of Hach's model sc sensors are "plug and play" with no complicated wiring or set-up procedure necessary.

---

Specifications

Accuracy:	Turbidity up to 1000 NTU:  without calibration < 5% of the measured value ±0.01 NTU  with calibration < 1% of the measured value ±0.01 NTU
Automatic wiper:	Yes
Body Material:	Stainless Steel
Cable length:	10 m (optional extension cables available)
Calibration method:	Turbidity Formazin or STABLCAL Standard (at 800 NTU). Requires a calibration kit. Suspended Solids Sample specific, based on gravimetric TSS analysis with a correction factor procedure
Certifications:	CE
Controller:	Sensor only
Diameter:	60 mm
Flow:	Max. 3 m/s (the presence of air bubbles affects the measurement)
Length:	200 mm
Maintenance interval:	1 h/month
Material:	Optics carrier and sleeve: PVC black  Wiper arm: stainless steel 1.4581  Wiper rubber: silicone rubber (standard)  Optional: FKM/FPM (LZX578)  Wiper shaft: stainless steel 1.4571
Max. cable length Sensor-to-Controller:	100 m
Measuring principle:	Infrared Duo scattered light technique for color-independent turbidity measurement. Turbidity in accordance with DIN EN ISO 7027 / TS equivalent DIN 38414
Measuring range:	TSS-content: 0.001 - 500 g/L; 0.001 - 500,000 mg/L (the upper range is dependent on the sample property)  Turbidity: 0.001 - 4000 NTU
Model:	Solitax hs-line sc
Mounting:	Immersion
Operating temperature range:	0 - 40 °C
Parameter:	High Range Suspended Solids, Turbidity
Pressure range:	Stainless steel immersion sensor: <6 bar or <60 m
Repeatability:	TSS content: < 3 %  Turbidity: < 1 %
Response time:	1 - 300 s adjustable
Warranty:	24 months
Weight:	1.38 kg
What's included?:	Turbidity/Suspended Solids probe, user manual

What's included?

Turbidity/Suspended Solids probe, user manual

---

## Required Accessories

- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 100-240 VAC, without power cord (Item LXV525.99A11551)
- SC4500 Controller, Prognosys, 5x mA Output, 1 digital Sensor, 100-240 VAC, without power cord (Item LXV525.99A11501)
- SC4500 Controller, Prognosys, 5x mA Output, 2 digital Sensors, 24 VDC, without plug (Item LXV525.99Z11551)