



Contacting Conductivity Gateway

Product #: 6120700.99
AED Price: Contact Hach

Digital Gateway is used to operate analog conductivity sensors of all ranges and connect them with a digital controller. Extension cables and the controller must be ordered separately.

Specifications

Calibration method:	Comparison to standard
Communication:	MODBUS
Conductivity accuracy:	± 2 % of reading
Diameter:	34 mm
Length:	175 mm
Measuring range:	1 - 2000 µS/cm if cell constant K=1.0
Operating humidity:	0 - 95 % relative humidity, non-condensing
Operating temperature range:	-20 - 60 °C at 0 - 95% RH (non-condensing)
Repeatability:	± 0.5 % of reading
Response time:	30 s
Storage conditions:	less than 95% Relative Humidity
Temperature accuracy:	± 0.1 °C
Weight:	0.145 kg
What's included?:	Includes: gateway, gateway user instructions

What's included?

Includes: gateway, gateway user instructions