



pH electrode with TOP68 connector

Product #: LZX540
AED Price: Contact Hach

High-pH-glass and single reference system, electrode for waster with high pH levels

Specifications

Cable connection:	TOP68 connector
Diameter:	12 mm
Diaphragm:	Ring diaphragm, porous PTFE
Immersion depth:	120 mm
Length:	140 mm
Material:	Sensor: Glass
Measuring range:	0 - 80 °C
Pressure range:	3.5 bar
Reference electrode:	Gel KCl/AgCl
Sensor thread:	Pg 13.5
Temperature sensor:	Pt100 integrated
Warranty:	6 months