



## Flow chamber, Polypropylene

**Product #:** C74451A1789A3

**AED Price:** Contact Hach

Flow fitting with PP union nut and 1 gasket (FKM/FPM), process connection 3/8–18 NPT

---

### Specifications

Diameter:	62 mm
Flow:	max 10 L/min
Height:	165 mm
Material:	Fitting: Polypropylene (PP)
Operating temperature range:	90 °C maximum
Pressure range:	max 1.5 bar at 20 °C
Process connection:	0.375 " NPT
Standard accessories:	Union nut and 1 gasket
Weight:	1.5 kg