



## Ball float mounting kit PVC for 1" electrochemical sensors

**Product #:** LZX914.99.42200

**AED Price:** Contact Hach

Mounting hardware for easy installation of sensors on the basin rim (railing or wall). Pole with ball float and pivoting and swiveling bracket. Used on sites with variable water levels.

---

### Specifications

Diameter:	48 mm
Length:	2300 mm immersion depth adjustable
Material:	PVC
Process connection:	CPVC clamp and stainless steel mounting bracket for the installation on the railing (max. diameter 2") or concrete wall
Special notes:	Composition:  Pole kit (2.3 m pipe, float, screw cap, etc.)  Pivoting and swiveling bracket (276G1200)  Sensor adapter (LZY276)