



## Sigmatrax 2 Sampling Unit, with 10 m connecting hose, w/o control unit

**Product #:** LXV231  
**AED Price:** Contact Hach

Supplies the Phosphax Sigma and TOCTAX process photometers with ultrasonically homogenised original samples for the determination of Total Phosphorus and TOC. Operation only with control unit.

---

### Specifications

Delivery height:	max. 7 m
Diameter:	184 mm probe
Hose length:	10 m
Length:	404 mm probe
Operating temperature range:	5 - 30 °C Sample
Power consumption:	250 VA
Warranty:	24 months
Weight:	7.5 kg probe with 10 m hose
What's included?:	Sampling Unit only, requires Sigmatrax 2 control unit

---

### What's included?

Sampling Unit only, requires Sigmatrax 2 control unit

---

### Required Accessories

- Sigmatrax 2 Control unit sampling & ultrasonic homogenisation (Item LXV215)