



## Sigmatrax 2 Sampling Unit, with 30 m connecting hose, w/o control unit

**Product #:** LXV282  
**AED Price:** Contact Hach

Using the immersed sampling probe the volume of sample necessary for the analysis is pumped without coming into contact with pumps.

The sample is delivered to a small glass vessel in the control unit and is homogenized using an ultrasonic generator.

---

### Specifications

Delivery height:	max. 7 m
Diameter:	184 mm Sonde
Hose length:	30 m
Length:	404 mm probe
Operating temperature range:	5 - 30 °C Sample
Power consumption:	470 VA
Warranty:	24 months
Weight:	22 kg probe with 30m hose
What's included?:	Sampling Unit only, requires Sigmatrax 2 control unit

---

### What's included?

Sampling Unit only, requires Sigmatrax 2 control unit

---

### Required Accessories

- Sigmatrax 2 Control unit sampling & ultrasonic homogenisation (Item LXV215)