



SC1000 Probe Module, 6 Sensor Connectors, Prognosys, Profibus DP, 100-240 VAC, with EU plug

Product #: LXV400.99.2S031

AED Price: Contact Hach

Local measurement of several parameters & confidence through the power of predictive insight

Probe module for connecting up to 6 SC sensors, with Profibus DP network interface card, and EU power cord for 100 - 240 V AC power supply. With Prognosys predictive diagnostics.

A controller system to which SC sensors can be connected and from which they can be controlled consists of a single SC1000 display module and one or more SC1000 probe modules. The system is configured modularly in line with customer-specific requirements and can be expanded at any time with additional measurement stations, sensors, inputs, outputs and bus interfaces.

The probe module is used to connect SC sensors to a measurement station. Several probe modules can be linked to create a SC1000 network.

Prognosys is a predictive diagnostic system that allows you to be proactive in your maintenance, by alerting you to upcoming instrument issues. Know with confidence whether changes in your measurements are due to changes in your instrument or your water.

Performance certified according to MCERTs regulation.

More confidence in your instrument's performance

Available exclusively on the SC1000, Prognosys predictive diagnostics uses patented multivariable diagnostic software to read multiple inputs from your instrument and alert you to the instrument's overall performance. An easy-to-read dashboard provides instant indication of measurement reliability and service requirements.

Plug and Play operation

There's no complicated wiring or set up procedures with the SC1000 controller. Plug any Hach digital sensor into a Probe Module and it's ready for use. No special ordering or software configuration is needed.

Communication options to fit any application need

The SC1000 controller features state-of-the art Modbus TCP/IP communications protocol for seamless integration into a network of devices that support TCP/IP sockets. Use a standard Ethernet cable or connect wirelessly using GSM/GPRS to communicate with your SCADA, PLC or other network. The SC1000 also offers up to 12 analogue outputs for measured values and up to 12 analog or digital values from non-digital sensors.

Expandable and upgradable

The SC1000 Controller can adapt to your needs. Add or change probes without having to change the controller. Plus, with a single Display Module, additional Probe Modules and associated sensors can be added or removed depending on operational needs. Fully upgradable software ensures that this system will not be obsolete. Hach service plans are available.

Specifications

Alarm:	Low alarm point, low alarm point deadband, high alarm point, high alarm point deadband, off delay, and on delay
Analog Output:	No Output Module
Analogue inputs:	No Input Module
Analogue output functional mode:	PID, high/low phasing, setpoint, deadband, overfeed timer, off delay, on delay
Analogue outputs:	Up to 12 analog/digital inputs scalable via digital network
Certifications:	European Certifications: CE per 73/23/EEC and 89/336/EEC TUV-GS to EN 61010-1 EN 61326 Amd's 1 & 2
Communication:	MODBUS (RS485): Advanced communications/networking with PLC or SCADA system directly from analyzer PROFIBUS DP/V1 (certified) GSM/GPRS Quad-band cellular module (FCC and IC approved, EU and US only) Ethernet service port, RJ45, 10 MB/s
Communication capabilities:	Profibus DP
Conduit for Relay Connection:	No
Dimensions (H x W x D):	242 mm x 315 mm x 120 mm
Display:	¼ inch VGA graphical backlit TFT color Glas/Glas-Touch screen, high resistance 320 x 240 pixels
Display resolution:	320 x 240 Pixel, 256 colours glass/glass-touch supplied by display module
Display viewing area:	11.4 x 8.6 cm
Electrical Certifications:	CE 2006/95/EC, EMV 2004/108/EC, TUV-GS EN61010-1, DIN EN 61329
Enclosure waterproof rating:	IP65
Inputs:	Up to 12 analogue 0-20 mA, maximum impedance 500 Ohms per probe module. Additional inputs are available with additional probe modules.
Material:	ABS (display module) and metal (probe module) enclosure with corrosion resistant finish
Mounting:	Surface, panel, and pipe (horizontal and vertical) with optional sun shield
Mounting configurations:	Surface, panel, and pipe (horizontal and vertical) with optional sun shield
Operating temperature range:	-20 - 55 °C / 0 - 95% relative humidity, non-condensing
Output:	Up to 12 analog 0/4-20 mA, maximum impedance 500 Ohms per probe module. Additional analog outputs with additional probe modules. Optional digital communications via Modbus® (RS485) and Profibus® DP/V1.
Power Options:	100-240V AC, EU Power Cord
Prognosys:	Yes
Relays:	No Relay
RTC Module:	No
Sensors:	6, additional sensor inputs available via digital network
Storage conditions:	-20 - 70 °C (-4 to 158 °F), 0 to 95% relative humidity, non-condensing
Warranty:	24 months
Weight:	Approximately 6.5 kg (depending on configuration)
What's included?:	SC1000 Probe Module with installed cards (as requested), Basic User Manual, EU Power Cord

What's included?

SC1000 Probe Module with installed cards (as requested), Basic User Manual, EU Power Cord