



SIP10 Sipper for DR3900

Product #: LQV157.99.00001
AED Price: Contact Hach

Sipper for pour through applications. Basic instrument without accessories.

Specifications

Dimensions (H x W x D):	120 mm x 85 mm x 200 mm
Flow rate:	1 mL/s
Interface:	USB type A
Operating temperature range:	10 - 40 °C at 95% Relative Humidity (non-condensing)
Power requirements (Voltage):	5 V
Power Supply:	USB Cable
Rinsing volume:	Minimum 25 mL
Storage conditions:	-10 °C - 60 °C
Warranty:	24 months
Wavelength range:	340 nm - 900 nm
Weight:	0.5 kg