



## High Output Airblast, 230V

**Product #:** 6860100.99.0002  
**AED Price:** Contact Hach

Automatic cleaning system for AN-ISE sc, A-ISE sc, N-ISE sc, LDO sc/LDO 2 sc

---

### Specifications

Depth:	compressor
Dimensions (H x W x D):	370 mm x 320 mm x 200 mm
Enclosure waterproof rating:	IP66 / NEMA 4X
Flow:	1 m <sup>3</sup> /h output Air Flow Rate at compressor outlet
Fuse:	250 V 5 A, controller relay
Height:	compressor
Max. duty cycle:	60 s for every 15 minutes
Measuring principle:	High output air blast system for attachment to select sensors to reduce biogrowth and other types of fouling
Operating temperature range:	-20 - 50 °C at 0 - 95% RH (non-condensing)
Power requirements (Hz):	50 Hz
Power requirements (Voltage):	230 V AC
Pressure range:	2.76 bar output air pressure at compressor outlet
Storage conditions:	-20 °C - 70 °C ; 95% Relative Humidity
Warranty:	24 months
Weight:	10.7 kg compressor
What's included?:	The following items are included as standard components of the self-cleaning kit:• Tubing, 7.6 m (25 ft)• Tie wraps• HOAB compressor with mounting hardware• Relay Barrier
Width:	compressor

---

### What's included?

The following items are included as standard components of the self-cleaning kit:• Tubing, 7.6 m (25 ft)• Tie wraps• HOAB compressor with mounting hardware• Relay Barrier